

Garant
KNUX 160410L, Grade: HB7010-1

Order data

Order number	251078 HB7010-1
GTIN	4045197780003
Item class	21G

Description

KNUX 160410L HB7010-1 Grade: HB7010-1

Chip breaker: SG

Chip diverter: 3.2 mm

Cutting depth a_p : 1 - 6 mm

Feed f : 0.2 - 0.5 mm/rev.

Cutting speed v_c main application: 100 - 375 m/min

Technical description

Corner radius	1 mm
Chip diverter	3.2 mm
Chip breaker	SG
Main application	P
Feed f	0.2 - 0.5 mm/rev.
Cutting conditions	continuous
Grade	HB7010-1
Cutting speed v_c main application	100 - 375 m/min
Cutting depth a_p	1 - 6 mm
Finishing/roughing assignment	Roughing

Tool material	Carbide
Number of changes/inserts	2
ISO code indexable insert	KNUX 160410L
Type of product	Indexable insert for turning