

Garant
CC.T 09T304, Grade: HB7010-1


Order data

Order number	260058 HB7010-1
GTIN	4045197780416
Item class	21G

Description

CC.T 09T304 HB7010-1 Grade: HB7010-1
 Chip breaker: SS
 Tolerance: M
 Cutting depth a_p : 0.2 - 2.5 mm
 Feed f : 0.05 - 0.25 mm/rev.
 Cutting speed v_c main application: 150 - 500 m/min

Technical description

Main application	P
Corner radius	0.4 mm
Cutting conditions	continuous
Cutting speed v_c main application	150 - 500 m/min
Feed f	0.05 - 0.25 mm/rev.
Cutting depth a_p	0.2 - 2.5 mm
Grade	HB7010-1

Chip breaker	SS
Finishing/roughing assignment	Finishing
Tool material	Carbide
ISO code indexable insert	CCMT 09T304
Number of changes/inserts	2
Tolerance	M
Type of product	Indexable insert for turning