

Garant
DC.T 11T308, Grade: HB7010-1


Order data

Order number	260464 HB7010-1
GTIN	4045197780607
Item class	21G

Description

DC.T 11T308 HB7010-1 Grade: HB7010-1
 Chip breaker: SM
 Tolerance: M
 Cutting depth a_p : 0.5 - 2.5 mm
 Feed f : 0.1 - 0.3 mm/rev.
 Cutting speed v_c main application: 120 - 440 m/min

Technical description

Cutting conditions	continuous
Grade	HB7010-1
Cutting speed v_c main application	120 - 440 m/min
Feed f	0.1 - 0.3 mm/rev.
Cutting depth a_p	0.5 - 2.5 mm
Main application	P
Chip breaker	SM

Corner radius	0.8 mm
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Carbide
ISO code indexable insert	DCMT 11T308
Number of changes/inserts	2
Tolerance	M
Type of product	Indexable insert for turning