

Garant**TCMT 110204, Grade: HB7010-1****Order data**

Order number	260952 HB7010-1
GTIN	4045197780683
Item class	21G

Description

TCMT 110204 HB7010-1 Grade: HB7010-1

Chip breaker: SS

Cutting depth a_p : 0.2 - 1.5 mmFeed f : 0.05 - 0.2 mm/rev.Cutting speed v_c main application: 150 - 500 m/min**Technical description**

Grade	HB7010-1
Cutting speed v_c main application	150 - 500 m/min
Cutting depth a_p	0.2 - 1.5 mm
Cutting conditions	continuous
Feed f	0.05 - 0.2 mm/rev.
Main application	P
Chip breaker	SS
Corner radius	0.4 mm

Finishing/roughing assignment	Finishing
Tool material	Carbide
ISO code indexable insert	TCMT 110204
Number of changes/inserts	3
Type of product	Indexable insert for turning