

Garant
TC.T 110202, Grade: HB7010-1


Order data

Order number	260980 HB7010-1
GTIN	4045197780706
Item class	21G

Description

TC.T 110202 HB7010-1 Grade: HB7010-1
 Chip breaker: SM
 Tolerance: M
 Cutting depth a_p : 0.5 - 2.5 mm
 Feed f : 0.1 - 0.3 mm/rev.
 Cutting speed v_c main application: 120 - 440 m/min

Technical description

Chip breaker	SM
Main application	P
Cutting conditions	continuous
Feed f	0.1 - 0.3 mm/rev.
Cutting depth a_p	0.5 - 2.5 mm
Cutting speed v_c main application	120 - 440 m/min
Grade	HB7010-1
Corner radius	0.2 mm

Finishing/roughing assignment	Semi-roughing
Tool material	Carbide
ISO code indexable insert	TCMT 110202
Number of changes/inserts	3
Tolerance	M
Type of product	Indexable insert for turning