

Garant
VBMT 160404, Grade: HB7010-1


Order data

Order number	261152 HB7010-1
GTIN	4045197780775
Item class	21G

Description

VBMT 160404 HB7010-1 Grade: HB7010-1
 Chip breaker: SS
 Cutting depth a_p : 0.2 - 1.5 mm
 Feed f : 0.05 - 0.2 mm/rev.
 Cutting speed v_c main application: 150 - 500 m/min

Technical description

Cutting conditions	continuous
Main application	P
Chip breaker	SS
Feed f	0.05 - 0.2 mm/rev.
Grade	HB7010-1
Cutting speed v_c main application	150 - 500 m/min
Cutting depth a_p	0.2 - 1.5 mm

Corner radius	0.4 mm
Finishing/roughing assignment	Finishing
Tool material	Carbide
ISO code indexable insert	VBMT 160404
Number of changes/inserts	2
Type of product	Indexable insert for turning