

Garant
VB.T 160408, Grade: HB7010-1


Order data

| | |
|--------------|-----------------|
| Order number | 261234 HB7010-1 |
| GTIN | 4045197780812 |
| Item class | 21G |

Description

VB.T 160408 HB7010-1 Grade: HB7010-1
 Chip breaker: SM
 Tolerance: M
 Cutting depth a_p : 0.5 - 2.5 mm
 Feed f : 0.1 - 0.3 mm/rev.
 Cutting speed v_c main application: 120 - 440 m/min

Technical description

| | |
|--------------------------------------|-----------------|
| Grade | HB7010-1 |
| Main application | P |
| Cutting depth a_p | 0.5 - 2.5 mm |
| Chip breaker | SM |
| Cutting conditions | continuous |
| Cutting speed v_c main application | 120 - 440 m/min |
| Corner radius | 0.8 mm |

| | |
|-------------------------------|------------------------------|
| Feed f | 0.1 - 0.3 mm/rev. |
| Finishing/roughing assignment | Semi-roughing |
| Tool material | Carbide |
| ISO code indexable insert | VBMT 160408 |
| Number of changes/inserts | 2 |
| Tolerance | M |
| Type of product | Indexable insert for turning |