

**Garant**
**VC.T 160408, Grade: HB7010-1**


### Order data

Order number	261459 HB7010-1
GTIN	4045197780881
Item class	21G

### Description

VC.T 160408 HB7010-1 Grade: HB7010-1  
 Chip breaker: SM  
 Tolerance: M  
 Cutting depth  $a_p$ : 0.5 - 2.5 mm  
 Feed  $f$ : 0.1 - 0.3 mm/rev.  
 Cutting speed  $v_c$  main application: 120 - 440 m/min

### Technical description

Chip breaker	SM
Feed $f$	0.1 - 0.3 mm/rev.
Corner radius	0.8 mm
Cutting depth $a_p$	0.5 - 2.5 mm
Cutting speed $v_c$ main application	120 - 440 m/min
Main application	P
Grade	HB7010-1

Cutting conditions	continuous
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Carbide
ISO code indexable insert	VCMT 160408
Number of changes/inserts	2
Tolerance	M
Type of product	Indexable insert for turning