

JEPSON POWER

Drytec® carbide circular saw blade Ø 355×25.4 mm, Number of teeth: 90


Order data

| | |
|--------------|---------------|
| Order number | 078237 90 |
| GTIN | 4260052460146 |
| Item class | 07E |

Description

Version:

Carbide-tipped circular saw blade for precise cutting.

- **Safety at work: Thin-walled, low-vibration, reduced noise.**
- **Extremely long working life.**
- **High-quality cutting.**
- **Can be resharpened 5x.**
- **General-purpose use for steel, plastic, and non-ferrous metals (not No. 078236).**

Note:

Other special saw blades for aluminium, stainless steel, for example, are available on request.

Technical description

| | |
|----------------------------|---------------------------------|
| No. of teeth optimised for | Material thickness up to 2.5 mm |
| Number of teeth | 90 |
| Width of cut B | 2.2 mm |
| suitable for | 078231 size 9435 |
| Suitable for material | for thin-walled material |

Type of product

Circular saw blade