

ELTEN
Shoe, black/red SENEX PRO ESD, S3, EU shoe size: 40


Order data

Order number	092246 40
GTIN	4030839254967
Item class	09P

Description

Version:

Safety shoe in the TRAINERS series.

- **Breathable textile lining.**
- **ESD PRO black full-size insole.**
- **TRAINERS TPU/PU sole, anti-slip.**
- **TPU overcap to protect the upper.**
- **Entire shoe contains no metal or leather.**
- **Safety reflectors.**
- **ESD security.**

Safety shoe of abrasion-resistant, **dirt and water-repellent** Cordura® material.

- **Particularly easy-care and quick drying.**
- **Free of metal and leather.**
- **Low weight means they are outstandingly comfortable to wear.**
- **Uppers of Fashmo™ hydrophobic microfibre and textile material of CORDURA®. Water-repellent and dirt-repellent, tear-resistant and abrasion-resistant, breathable.**
- **Closed, padded tongue.**

Standard:

EN ISO 20345:2011 S3 SRC

Einlagenversorgung baumustergeprüft nach DGUV Regel 191.

Note:

Stock goods in EU sizes 39 – 46, can be ordered in EU sizes 38 – 47.

electrostatic characteristic: EGB/ESD

Protection class: S3

Material of protective toe-cap: Composite

Puncture resistance: Textile

Standard: Inlay type-tested according to DGUV regulation 191

Technical description

Uppers material	Cordura®
Puncture resistance	Textile
Protection class	S3
Colour	black/red
EU shoe size	40
suitable for orthopaedic insoles	yes
Material of protective toe-cap	Composite
with reflective material (good visibility)	yes
contains no metal or leather	yes
Material of outer sole	TPU/PU
Standard	Inlay type-tested according to DGUV regulation 191
Series	SENEX
Gender	Gentlemen's
electrostatic characteristic	EGB/ESD
Type of product	Safety shoes