



**Welder's boots, black CARL HI, S3, EU shoe size: 40**



**Order data**

|              |               |
|--------------|---------------|
| Order number | 092255 40     |
| GTIN         | 4030839210437 |
| Item class   | 09P           |

**Description**

**Version:**

Welder's boot with excellent thermal properties. Heat-resistant up to approx. 200 °C, for short periods up to 300 °C.

- **Upper material of sturdy cowhide.**
- **Leather lining.**
- **Closed tongue.**
- **Basic grey full-size insole.**
- **Anti-static soft fleece fire sole.**
- **Deep-tread rubber/PU SAFETY-GRIP sole.**
- **PU toe protection.**
- **Heat-resistant seams.**
- **Quick release for easy entry.**
- **Padded spark protection sleeve.**

**Standard:**

EN ISO 20345:2011 S3 SRC HI HRO

Einlagenversorgung baumustergeprüft nach DGUV Regel 191.

**Note:**

Stock goods in EU sizes 39 – 46, can be ordered in EU sizes 39 – 48.

Protection class: S3

Material of protective toe-cap: Steel

Puncture resistance: Steel

Behaviour of outer sole in response to contact temperature (melting point of the outer sole):  
Over 200 °C

Standard: Inlay type-tested according to DGUV regulation 191

## Technical description

|  |  |
|--|--|
| Behaviour of outer sole in response to contact temperature (melting point of the outer sole) | Over 200 °C  |
| Material of outer sole   | Rubber/PU  |
| Material of protective toe-cap   | Steel  |
| EU shoe size   | 40   |
| Uppers material  | Genuine leather                                    |
| Colour   | black  |
| Puncture resistance  | Steel  |
| Protection class   | S3   |
| Standard   | Inlay type-tested according to DGUV regulation 191 |
| Material inner lining  | Leather  |
| Series   | CARL   |
| Gender   | Gentlemen's  |
| Type of product  | Safety boots                                       |