



**Welder's boots, black CARL HI, S3, EU shoe size: 41**



**Order data**

Order number	092255 41
GTIN	4030839210444
Item class	09P

**Description**

**Version:**

Welder's boot with excellent thermal properties. Heat-resistant up to approx. 200 °C, for short periods up to 300 °C.

- **Upper material of sturdy cowhide.**
- **Leather lining.**
- **Closed tongue.**
- **Basic grey full-size insole.**
- **Anti-static soft fleece fire sole.**
- **Deep-tread rubber/PU SAFETY-GRIP sole.**
- **PU toe protection.**
- **Heat-resistant seams.**
- **Quick release for easy entry.**
- **Padded spark protection sleeve.**

**Standard:**

EN ISO 20345:2011 S3 SRC HI HRO

Einlagenversorgung baumustergeprüft nach DGUV Regel 191.

**Note:**

Stock goods in EU sizes 39 – 46, can be ordered in EU sizes 39 – 48.

Protection class: S3

Material of protective toe-cap: Steel

Puncture resistance: Steel

Behaviour of outer sole in response to contact temperature (melting point of the outer sole):  
Over 200 °C

Standard: Inlay type-tested according to DGUV regulation 191

### Technical description

Uppers material	Genuine leather
EU shoe size	41
Protection class	S3
Material inner lining	Leather
Material of outer sole	Rubber/PU
Material of protective toe-cap	Steel
Puncture resistance	Steel
Behaviour of outer sole in response to contact temperature (melting point of the outer sole)	Over 200 °C
Colour	black
Standard	Inlay type-tested according to DGUV regulation 191
Series	CARL
Gender	Gentlemen's
Type of product	Safety boots