



Welder's boots, black CARL HI, S3, EU shoe size: 42



Order data

Order number	092255 42
GTIN	4030839210451
Item class	09P

Description

Version:

Welder's boot with excellent thermal properties. Heat-resistant up to approx. 200 °C, for short periods up to 300 °C.

- **Upper material of sturdy cowhide.**
- **Leather lining.**
- **Closed tongue.**
- **Basic grey full-size insole.**
- **Anti-static soft fleece fire sole.**
- **Deep-tread rubber/PU SAFETY-GRIP sole.**
- **PU toe protection.**
- **Heat-resistant seams.**
- **Quick release for easy entry.**
- **Padded spark protection sleeve.**

Standard:

EN ISO 20345:2011 S3 SRC HI HRO

Einlagenversorgung baumustergeprüft nach DGUV Regel 191.

Note:

Stock goods in EU sizes 39 – 46, can be ordered in EU sizes 39 – 48.

Protection class: S3

Material of protective toe-cap: Steel

Puncture resistance: Steel

Behaviour of outer sole in response to contact temperature (melting point of the outer sole):
Over 200 °C

Standard: Inlay type-tested according to DGUV regulation 191

Technical description

Material inner lining	Leather
Protection class	S3
Standard	Inlay type-tested according to DGUV regulation 191
Uppers material	Genuine leather
EU shoe size	42
Behaviour of outer sole in response to contact temperature (melting point of the outer sole)	Over 200 °C
Puncture resistance	Steel
Material of protective toe-cap	Steel
Colour	black
Material of outer sole	Rubber/PU
Series	CARL
Gender	Gentlemen's
Type of product	Safety boots