



Welder's boots, black CARL HI, S3, EU shoe size: 43



Order data

| | |
|--------------|---------------|
| Order number | 092255 43 |
| GTIN | 4030839210468 |
| Item class | 09P |

Description

Version:

Welder's boot with excellent thermal properties. Heat-resistant up to approx. 200 °C, for short periods up to 300 °C.

- **Upper material of sturdy cowhide.**
- **Leather lining.**
- **Closed tongue.**
- **Basic grey full-size insole.**
- **Anti-static soft fleece fire sole.**
- **Deep-tread rubber/PU SAFETY-GRIP sole.**
- **PU toe protection.**
- **Heat-resistant seams.**
- **Quick release for easy entry.**
- **Padded spark protection sleeve.**

Standard:

EN ISO 20345:2011 S3 SRC HI HRO

Einlagenversorgung baumustergeprüft nach DGUV Regel 191.

Note:

Stock goods in EU sizes 39 – 46, can be ordered in EU sizes 39 – 48.

Protection class: S3

Material of protective toe-cap: Steel

Puncture resistance: Steel

Behaviour of outer sole in response to contact temperature (melting point of the outer sole):
Over 200 °C

Standard: Inlay type-tested according to DGUV regulation 191

Technical description

| Behaviour of outer sole in response to contact temperature (melting point of the outer sole) | Over 200 °C |
|--|--|
| Protection class | S3 |
| Standard | Inlay type-tested according to DGUV regulation 191 |
| Puncture resistance | Steel |
| Material of protective toe-cap | Steel |
| Material of outer sole | Rubber/PU |
| Colour | black |
| Uppers material | Genuine leather |
| Material inner lining | Leather |
| EU shoe size | 43 |
| Series | CARL |
| Gender | Gentlemen's |
| Type of product | Safety boots |