



Welder's boots, black CARL HI, S3, EU shoe size: 45



Order data

Order number	092255 45
GTIN	4030839210482
Item class	09P

Description

Version:

Welder's boot with excellent thermal properties. Heat-resistant up to approx. 200 °C, for short periods up to 300 °C.

- **Upper material of sturdy cowhide.**
- **Leather lining.**
- **Closed tongue.**
- **Basic grey full-size insole.**
- **Anti-static soft fleece fire sole.**
- **Deep-tread rubber/PU SAFETY-GRIP sole.**
- **PU toe protection.**
- **Heat-resistant seams.**
- **Quick release for easy entry.**
- **Padded spark protection sleeve.**

Standard:

EN ISO 20345:2011 S3 SRC HI HRO

Einlagenversorgung baumustergeprüft nach DGUV Regel 191.

Note:

Stock goods in EU sizes 39 – 46, can be ordered in EU sizes 39 – 48.

Protection class: S3

Material of protective toe-cap: Steel

Puncture resistance: Steel

Behaviour of outer sole in response to contact temperature (melting point of the outer sole):
 Over 200 °C
 Standard: Inlay type-tested according to DGUV regulation 191

Technical description

Standard	Inlay type-tested according to DGUV regulation 191
Uppers material	Genuine leather
Colour	black
Material inner lining	Leather
Material of protective toe-cap	Steel
Puncture resistance	Steel
Behaviour of outer sole in response to contact temperature (melting point of the outer sole)	Over 200 °C
Protection class	S3
Material of outer sole	Rubber/PU
EU shoe size	45
Series	CARL
Gender	Gentlemen's
Type of product	Safety boots