



**Welder's boots, black CARL HI, S3, EU shoe size: 48**



**Order data**

Order number	092255 48
GTIN	4030839210512
Item class	09P

**Description**

**Version:**

Welder's boot with excellent thermal properties. Heat-resistant up to approx. 200 °C, for short periods up to 300 °C.

- **Upper material of sturdy cowhide.**
- **Leather lining.**
- **Closed tongue.**
- **Basic grey full-size insole.**
- **Anti-static soft fleece fire sole.**
- **Deep-tread rubber/PU SAFETY-GRIP sole.**
- **PU toe protection.**
- **Heat-resistant seams.**
- **Quick release for easy entry.**
- **Padded spark protection sleeve.**

**Standard:**

EN ISO 20345:2011 S3 SRC HI HRO

Einlagenversorgung baumustergeprüft nach DGUV Regel 191.

**Note:**

Stock goods in EU sizes 39 – 46, can be ordered in EU sizes 39 – 48.

Protection class: S3

Material of protective toe-cap: Steel

Puncture resistance: Steel

Behaviour of outer sole in response to contact temperature (melting point of the outer sole):  
Over 200 °C

Standard: Inlay type-tested according to DGUV regulation 191

### Technical description

Material of outer sole	Rubber/PU
Material of protective toe-cap	Steel
Uppers material	Genuine leather
Standard	Inlay type-tested according to DGUV regulation 191
Protection class	S3
Puncture resistance	Steel
Colour	black
EU shoe size	48
Material inner lining	Leather
Behaviour of outer sole in response to contact temperature (melting point of the outer sole)	Over 200 °C
Series	CARL
Gender	Gentlemen's
Type of product	Safety boots