



Lace-up boot, grey/blue VX 769 Bau Perbunan, S3 NB, EU shoe size: 40



Order data

Order number	092801 40
GTIN	4044348485156
Item class	09C

Description

Version:

VX 769 Perbunan lace-up boots with uppers of smooth supple leather combined with soft Nubuk leather.

- **Closed tongue.**
- **Safety reflectors.**
- **Sole tread Perbunan VX, grey-blue.**
- **Reinforced protection against penetration.**
- **Real leather inner sole.**
- **ERGO-COOL® ESD comfort footbed inlay.**

Standard:

EN ISO 20345:2011 S3 SRC CI HRO

Note:

Wide version XB, see No. 092802.

EU shoe sizes 39 – 46 held in stock, EU shoe sizes 38 – 48 can be ordered.

Note re advertising text:

Safety shoes from STEITZ SECURA offer a multi-width system.

Protection class: S3

Material of protective toe-cap: Steel

Behaviour of outer sole in response to contact temperature (melting point of the outer sole):

Over 200°C °C

Cold insulation: Down to -20°C

Norm: Inlay type-tested according to DGUV regulation 191

Technical description

Behaviour of outer sole in response to contact temperature (melting point of the outer sole)	Over 200 °C °C
EU shoe size	40
Slip resistance	yes
with reflective material (good visibility)	yes
Cold insulation	down to -20°C
Norm	Inlay type-tested according to DGUV regulation 191
Protection class	S3
Material of protective toe-cap	Steel
Uppers material	Smooth leather
Puncture resistance	Steel
Colour	black
cut-resistant	yes
Material of outer sole	Perbunan VX
Series	VX 700
Gender	Gentlemen's
Type of product	Safety boots