



Lace-up boot, grey/blue VX 769 Bau Perbunan, S3 XB, EU shoe size: 38



Order data

Order number	092802 38
GTIN	4044348485248
Item class	09C

Description

Version:

Safety shoes of supple smooth leather with broad tread face and **high heat resistance** up to approx. 220°C.

- **Closed tongue.**
- **ERGO-COOL full-size comfort insole with ventilation structure for optimum climatic comfort.**
- **Perbunan VX outer sole.**
- **Very good abrasion resistance and non-slip properties.**
- **High cut resistance and mechanical stress resistance.**

VX 769 Perbunan lace-up boots with uppers of smooth supple leather combined with soft Nubuk leather.

- **Closed tongue.**
- **Safety reflectors.**
- **Sole tread Perbunan VX, grey-blue.**
- **Reinforced protection against penetration.**
- **Real leather inner sole.**
- **ERGO-COOL® ESD comfort footbed inlay.**

Standard:

EN ISO 20345:2011 S3 SRC CI HRO

Note:

EU shoe sizes 39 – 46 held in stock, EU shoe sizes 38 – 48 can be ordered.

Protection class: S2

Material of protective toe-cap: Aluminium

Behaviour of outer sole in response to contact temperature (melting point of the outer sole):
Over 200°C °C

Norm: Inlay type-tested according to DGUV regulation 191

Technical description

Protection class	S2
cut-resistant	yes
Material of protective toe-cap	Aluminium
Slip resistance	yes
Material of outer sole	Perbunan VX
Norm	Inlay type-tested according to DGUV regulation 191
Colour	black
EU shoe size	38
with reflective material (good visibility)	yes
Behaviour of outer sole in response to contact temperature (melting point of the outer sole)	Over 200 °C °C
Uppers material	Smooth leather
Series	VX 700
Gender	Gentlemen's
Type of product	Safety boots