



Lace-up boot, grey/blue VX 769 Bau Perbunan, S3 XB, EU shoe size: 39



Order data

| | |
|--------------|---------------|
| Order number | 092802 39 |
| GTIN | 4044348485255 |
| Item class | 09C |

Description

Version:

Safety shoes of supple smooth leather with broad tread face and **high heat resistance** up to approx. 220°C.

- **Closed tongue.**
- **ERGO-COOL full-size comfort insole with ventilation structure for optimum climatic comfort.**
- **Perbunan VX outer sole.**
- **Very good abrasion resistance and non-slip properties.**
- **High cut resistance and mechanical stress resistance.**

VX 769 Perbunan lace-up boots with uppers of smooth supple leather combined with soft Nubuk leather.

- **Closed tongue.**
- **Safety reflectors.**
- **Sole tread Perbunan VX, grey-blue.**
- **Reinforced protection against penetration.**
- **Real leather inner sole.**
- **ERGO-COOL® ESD comfort footbed inlay.**

Standard:

EN ISO 20345:2011 S3 SRC CI HRO

Note:

EU shoe sizes 39 – 46 held in stock, EU shoe sizes 38 – 48 can be ordered.

Protection class: S2

Material of protective toe-cap: Aluminium

Behaviour of outer sole in response to contact temperature (melting point of the outer sole):
Over 200°C °C

Norm: Inlay type-tested according to DGUV regulation 191

Technical description

| | |
|--|--|
| Slip resistance | yes |
| Material of outer sole | Perbunan VX |
| Behaviour of outer sole in response to contact temperature (melting point of the outer sole) | Over 200 °C °C |
| cut-resistant | yes |
| with reflective material (good visibility) | yes |
| Protection class | S2 |
| Material of protective toe-cap | Aluminium |
| Uppers material | Smooth leather |
| EU shoe size | 39 |
| Norm | Inlay type-tested according to DGUV regulation 191 |
| Colour | black |
| Series | VX 700 |
| Gender | Gentlemen's |
| Type of product | Safety boots |