



## Lace-up boot, grey/blue VX 769 Bau Perbunan, S3 XB, EU shoe size: 44



### Order data

Order number	092802 44
GTIN	4044348485309
Item class	09C

### Description

#### Version:

Safety shoes of supple smooth leather with broad tread face and **high heat resistance** up to approx. 220°C.

- **Closed tongue.**
- **ERGO-COOL full-size comfort insole with ventilation structure for optimum climatic comfort.**
- **Perbunan VX outer sole.**
- **Very good abrasion resistance and non-slip properties.**
- **High cut resistance and mechanical stress resistance.**

VX 769 Perbunan lace-up boots with uppers of smooth supple leather combined with soft Nubuk leather.

- **Closed tongue.**
- **Safety reflectors.**
- **Sole tread Perbunan VX, grey-blue.**
- **Reinforced protection against penetration.**
- **Real leather inner sole.**
- **ERGO-COOL® ESD comfort footbed inlay.**

#### Standard:

EN ISO 20345:2011 S3 SRC CI HRO

#### Note:

EU shoe sizes 39 – 46 held in stock, EU shoe sizes 38 – 48 can be ordered.

Protection class: S2

Material of protective toe-cap: Aluminium

Behaviour of outer sole in response to contact temperature (melting point of the outer sole):  
Over 200°C °C

Norm: Inlay type-tested according to DGUV regulation 191

## Technical description

Norm	Inlay type-tested according to DGUV regulation 191
Slip resistance	yes
EU shoe size	44
Protection class	S2
with reflective material (good visibility)	yes
Behaviour of outer sole in response to contact temperature (melting point of the outer sole)	Over 200 °C °C
Colour	black
Material of outer sole	Perbunan VX
cut-resistant	yes
Material of protective toe-cap	Aluminium
Uppers material	Smooth leather
Series	VX 700
Gender	Gentlemen's
Type of product	Safety boots