



## Lace-up boot, grey/blue VX 769 Bau Perbunan, S3 XB, EU shoe size: 48



### Order data

Order number	092802 48
GTIN	4044348485347
Item class	09C

### Description

#### Version:

Safety shoes of supple smooth leather with broad tread face and **high heat resistance** up to approx. 220°C.

- **Closed tongue.**
- **ERGO-COOL full-size comfort insole with ventilation structure for optimum climatic comfort.**
- **Perbunan VX outer sole.**
- **Very good abrasion resistance and non-slip properties.**
- **High cut resistance and mechanical stress resistance.**

VX 769 Perbunan lace-up boots with uppers of smooth supple leather combined with soft Nubuk leather.

- **Closed tongue.**
- **Safety reflectors.**
- **Sole tread Perbunan VX, grey-blue.**
- **Reinforced protection against penetration.**
- **Real leather inner sole.**
- **ERGO-COOL® ESD comfort footbed inlay.**

#### Standard:

EN ISO 20345:2011 S3 SRC CI HRO

#### Note:

EU shoe sizes 39 – 46 held in stock, EU shoe sizes 38 – 48 can be ordered.

Protection class: S2

Material of protective toe-cap: Aluminium

Behaviour of outer sole in response to contact temperature (melting point of the outer sole):  
Over 200°C °C

Norm: Inlay type-tested according to DGUV regulation 191

## Technical description

cut-resistant	yes
with reflective material (good visibility)	yes
Norm	Inlay type-tested according to DGUV regulation 191
Material of protective toe-cap	Aluminium
Material of outer sole	Perbunan VX
Behaviour of outer sole in response to contact temperature (melting point of the outer sole)	Over 200 °C °C
EU shoe size	48
Colour	black
Slip resistance	yes
Uppers material	Smooth leather
Protection class	S2
Series	VX 700
Gender	Gentlemen's
Type of product	Safety boots