



Welder's boots, anthracite VX 7380 Perbunan ESD, S2 NB, EU shoe size: 38



Order data

Order number	092811 38
GTIN	4044348460405
Item class	09C

Description

Version:

Foundryman's and welder's boot VX 7380 Perbunan for extreme conditions. Gutter system for draining hot liquids.

- **Closed flap.**
- **Perbunan VX ESD sole, anthracite.**
- **SECURA VARIO® heel cushioning.**
- **Real leather inner sole.**
- **ERGO-COOL® comfort footbed insole.**
- **Protection against electrostatic discharges (ESD).**

Standard:

EN ISO 20349:2010 SRC WG WRU FO HRO

Note:

Wide version XB, see No. 092812.

EU shoe sizes 39 – 46 held in stock, EU shoe sizes 38 – 48 can be ordered.

Note re advertising text:

Safety shoes from Steitz Secura offer a multi-width system.

electrical insulation: EGB/ESD

Protection class: S2

Material of protective toe-cap: Aluminium

Behaviour of outer sole in response to contact temperature (melting point of the outer sole):

Over 200 °C °C

Norm: Inlay type-tested according to DGUV regulation 191
Characteristics: Vario® damping

Technical description

Colour	black
EU shoe size	38
Uppers material	Smooth leather
Slip resistance	yes
Material inner lining	Real leather
Norm	Inlay type-tested according to DGUV regulation 191
Material of protective toe-cap	Aluminium
cut-resistant	yes
Protection class	S2
Behaviour of outer sole in response to contact temperature (melting point of the outer sole)	Over 200 °C °C
Material of outer sole	Perbunan VX
Series	VX 7000
Characteristics	Vario® damping
Gender	Gentlemen's
electrical insulation	EGB/ESD
Type of product	Safety boots