



## Welder's boots, anthracite VX 7380 Perbunan ESD, S2 NB, EU shoe size: 44



### Order data

Order number	092811 44
GTIN	4044348460467
Item class	09C

### Description

#### Version:

**Foundryman's and welder's boot** VX 7380 Perbunan for extreme conditions. Gutter system for draining hot liquids.

- **Closed flap.**
- **Perbunan VX ESD sole, anthracite.**
- **SECURA VARIO® heel cushioning.**
- **Real leather inner sole.**
- **ERGO-COOL® comfort footbed insole.**
- **Protection against electrostatic discharges (ESD).**

#### Standard:

EN ISO 20349:2010 SRC WG WRU FO HRO

#### Note:

Wide version XB, see No. 092812.

EU shoe sizes 39 – 46 held in stock, EU shoe sizes 38 – 48 can be ordered.

#### Note re advertising text:

Safety shoes from Steitz Secura offer a multi-width system.

electrical insulation: EGB/ESD

Protection class: S2

Material of protective toe-cap: Aluminium

Behaviour of outer sole in response to contact temperature (melting point of the outer sole):

Over 200 °C °C

Norm: Inlay type-tested according to DGUV regulation 191  
 Characteristics: Vario® damping

## Technical description

Slip resistance	yes
Protection class	S2
Uppers material	Smooth leather
Material of outer sole	Perbunan VX
Behaviour of outer sole in response to contact temperature (melting point of the outer sole)	Over 200 °C °C
EU shoe size	44
Material of protective toe-cap	Aluminium
Material inner lining	Real leather
Norm	Inlay type-tested according to DGUV regulation 191
Colour	black
cut-resistant	yes
Series	VX 7000
Characteristics	Vario® damping
Gender	Gentlemen's
electrical insulation	EGB/ESD
Type of product	Safety boots