



## Welder's boots, anthracite VX 7380 Perbunan ESD, S2 XB, EU shoe size: 40



### Order data

|              |               |
|--------------|---------------|
| Order number | 092812 40     |
| GTIN         | 4044348342893 |
| Item class   | 09C           |

### Description

#### Version:

Safety shoes of supply smooth leather with broad tread face and **high heat resistance** up to approx. 220 °C.

- **Closed tongue.**
- **ERGO-COOL full-size comfort insole with ventilation structure for optimum climatic comfort.**
- **Perbunan VX outer sole.**
- **Very good resistance to abrasion and non-slip properties.**
- **High level of cutting resistance and mechanical strength.**

Foundryman's and welder's boots VX 7380 Perbunan for extreme conditions. Gutter system to allow hot liquids to run off.

- **Closed tongue.**
- **Sole tread Perbunan VX ESD, anthracite.**
- **SECURA VARIO® resilient heel.**
- **Real leather inner sole.**
- **ERGO-COOL® ESD comfort footbed inlay.**
- **Protection against electrostatic discharge (ESD).**

#### Standard:

EN ISO 20349:2010 SRC WG WRU FO HRO

#### Note:

EU shoe sizes 39 – 46 held in stock, EU shoe sizes 38 – 48 can be ordered.

electrical insulation: EGB/ESD

Protection class: S2

Material of protective toe-cap: Aluminium

Behaviour of outer sole in response to contact temperature (melting point of the outer sole):

Over 200 °C °C

Norm: Indlægsforsyning typegodkendt iht. DGUV-regel 191

Characteristics: Vario® damping

## Technical description

|  |   |
|--|---|
| Norm   | Indlægsforsyning typegodkendt iht. DGUV-regel 191 |
| Material inner lining  | Real leather                                      |
| Behaviour of outer sole in response to contact temperature (melting point of the outer sole) | Over 200 °C °C                                    |
| EU shoe size   | 40  |
| Material of outer sole   | Perbunan VX                                       |
| Protection class   | S2  |
| Colour   | black   |
| Uppers material  | Smooth leather                                    |
| Slip resistance  | yes   |
| cut-resistant  | yes   |
| Material of protective toe-cap   | Aluminium   |
| Series   | VX 7000   |
| Characteristics  | Vario® damping                                    |
| Gender   | Gentlemen's                                       |
| electrical insulation  | EGB/ESD   |
| Type of product  | Safety boots                                      |