



Welder's boots, anthracite VX 7380 Perbunan ESD, S2 XB, EU shoe size: 41



Order data

Order number	092812 41
GTIN	4044348460542
Item class	09C

Description

Version:

Safety shoes of supply smooth leather with broad tread face and **high heat resistance** up to approx. 220 °C.

- **Closed tongue.**
- **ERGO-COOL full-size comfort insole with ventilation structure for optimum climatic comfort.**
- **Perbunan VX outer sole.**
- **Very good resistance to abrasion and non-slip properties.**
- **High level of cutting resistance and mechanical strength.**

Foundryman's and welder's boots VX 7380 Perbunan for extreme conditions. Gutter system to allow hot liquids to run off.

- **Closed tongue.**
- **Sole tread Perbunan VX ESD, anthracite.**
- **SECURA VARIO® resilient heel.**
- **Real leather inner sole.**
- **ERGO-COOL® ESD comfort footbed inlay.**
- **Protection against electrostatic discharge (ESD).**

Standard:

EN ISO 20349:2010 SRC WG WRU FO HRO

Note:

EU shoe sizes 39 – 46 held in stock, EU shoe sizes 38 – 48 can be ordered.

electrical insulation: EGB/ESD

Protection class: S2

Material of protective toe-cap: Aluminium

Behaviour of outer sole in response to contact temperature (melting point of the outer sole):

Over 200 °C °C

Norm: Indlægsforsyning typegodkendt iht. DGUV-regel 191

Characteristics: Vario® damping

Technical description

Protection class	S2
Colour	black
cut-resistant	yes
Material of protective toe-cap	Aluminium
Slip resistance	yes
Material inner lining	Real leather
Norm	Indlægsforsyning typegodkendt iht. DGUV-regel 191
Material of outer sole	Perbunan VX
Uppers material	Smooth leather
EU shoe size	41
Behaviour of outer sole in response to contact temperature (melting point of the outer sole)	Over 200 °C °C
Series	VX 7000
Characteristics	Vario® damping
Gender	Gentlemen's
electrical insulation	EGB/ESD
Type of product	Safety boots