



Welder's boots, anthracite VX 7380 Perbunan ESD, S2 XB, EU shoe size: 45



Order data

Order number	092812 45
GTIN	4044348342947
Item class	09C

Description

Version:

Safety shoes of supply smooth leather with broad tread face and **high heat resistance** up to approx. 220 °C.

- **Closed tongue.**
- **ERGO-COOL full-size comfort insole with ventilation structure for optimum climatic comfort.**
- **Perbunan VX outer sole.**
- **Very good resistance to abrasion and non-slip properties.**
- **High level of cutting resistance and mechanical strength.**

Foundryman's and welder's boots VX 7380 Perbunan for extreme conditions. Gutter system to allow hot liquids to run off.

- **Closed tongue.**
- **Sole tread Perbunan VX ESD, anthracite.**
- **SECURA VARIO® resilient heel.**
- **Real leather inner sole.**
- **ERGO-COOL® ESD comfort footbed inlay.**
- **Protection against electrostatic discharge (ESD).**

Standard:

EN ISO 20349:2010 SRC WG WRU FO HRO

Note:

EU shoe sizes 39 – 46 held in stock, EU shoe sizes 38 – 48 can be ordered.

electrical insulation: EGB/ESD

Protection class: S2

Material of protective toe-cap: Aluminium

Behaviour of outer sole in response to contact temperature (melting point of the outer sole):

Over 200 °C °C

Norm: Indlægsforsyning typegodkendt iht. DGUV-regel 191

Characteristics: Vario® damping

Technical description

Material of protective toe-cap	Aluminium
Norm	Indlægsforsyning typegodkendt iht. DGUV-regel 191
Behaviour of outer sole in response to contact temperature (melting point of the outer sole)	Over 200 °C °C
Protection class	S2
Material of outer sole	Perbunan VX
cut-resistant	yes
Material inner lining	Real leather
Slip resistance	yes
Colour	black
EU shoe size	45
Uppers material	Smooth leather
Series	VX 7000
Characteristics	Vario® damping
Gender	Gentlemen's
electrical insulation	EGB/ESD
Type of product	Safety boots