



## Low-profile shoe, black/violet Vitality Plus 439 ESD, S2 XB, EU shoe size: 39



### Order data

Order number	092712 39
GTIN	4044348453933
Item class	09C

### Description

#### Version:

VITALITY PLUS low-profile ladies' safety shoes with **SECURA VARIO Vitality® multi-zone damping** and **STEITZ FLEX-ZONE®** sole tread with flexure zone.

- **Ultra-light functional outer material with breathable textile inserts.**
- **Closed tongue.**
- **Safety reflectors.**
- **ERGO-SOFT ESD comfort footbed inlay.**
- **Real leather inner sole.**
- **TPU-Dynamics sole tread, white.**
- **Protection against electrostatic discharge (ESD).**

Low-profile shoe with closed tongue and real leather upper sole.

- **Aluminium toecap.**
- **TPU-Dynamics sole.**
- **Lightweight sole structure with waisted instep.**

#### Standard:

EN ISO 20345:2011 S2 SRC

#### Note:

EU shoe sizes 36 – 41 held in stock, EU shoe sizes 35 – 42 can be ordered.

electrical insulation: EGB/ESD

Protection class: S2

Puncture resistance: Textile

Norm: Inlay type-tested according to DGUV regulation 191

## Technical description

Slip resistance	yes
Colour	black/violet
Puncture resistance	Textile
Protection class	S2
Material of outer sole	TPU Dynamics
EU shoe size	39
Norm	Inlay type-tested according to DGUV regulation 191
Gender	Gentlemen's
electrical insulation	EGB/ESD
Type of product	Safety shoes