



Swivel eye bolt SEB, Thread Ø: M8



Order data

Order number	086467 M8
GTIN	2050001857378
Item class	08Y

Description

Version:

High-strength swivel eye bolts, can be rotated through 360°, painted red.

Note:

SF 5:1 = Safety Factor 5.

SF 4:1 = Safety Factor 4.

Lifting capacity WLL SF 5:1: 0.4 t

Lifting capacity WLL SF 4:1: 0.5 t

Thread length L: 14 mm

Hole centre spacing x: 20 mm

Internal Ø ring A: 30 mm

External Ø ring B: 34 mm

Technical description

External Ø ring B	34 mm
Collar Ø support C	60 mm
Version	pivotable

Dimension D	57 mm
Internal Ø ring A	30 mm
Safe working load	0.3 t
Hole centre spacing x	20 mm
Internal hexagon size across flats S	6 mm
Lifting capacity WLL SF 4:1	0.5 t
Lifting capacity WLL SF 5:1	0.4 t
Thread length L	14 mm
Type of product	Eye bolt