

**Swivel eye bolt SEB, Thread Ø: M10****Order data**

Order number	086467 M10
GTIN	2050001857507
Item class	08Y

Description**Version:**

High-strength swivel eye bolts, can be rotated through 360°, painted red.

Note:

SF 5:1 = Safety Factor 5.

SF 4:1 = Safety Factor 4.

Lifting capacity WLL SF 5:1: 0.5 t

Lifting capacity WLL SF 4:1: 0.7 t

Thread length L: 17 mm

Hole centre spacing x: 20 mm

Internal Ø ring A: 30 mm

External Ø ring B: 34 mm

Technical description

Internal Ø ring A	30 mm
Version	pivotable
Collar Ø support C	60 mm

Dimension D	57 mm
Safe working load	0.6 t
External Ø ring B	34 mm
Hole centre spacing x	20 mm
Internal hexagon size across flats S	6 mm
Lifting capacity WLL SF 5:1	0.5 t
Lifting capacity WLL SF 4:1	0.7 t
Thread length L	17 mm
Type of product	Eye bolt