



Swivel eye bolt SEB, Thread \varnothing : M12



Order data

Order number	086467 M12
GTIN	2050001858153
Item class	08Y

Description

Version:

High-strength swivel eye bolts, can be rotated through 360°, painted red.

Note:

SF 5:1 = Safety Factor 5.

SF 4:1 = Safety Factor 4.

Lifting capacity WLL SF 5:1: 0.8 t

Lifting capacity WLL SF 4:1: 0.9 t

Thread length L: 21 mm

Hole centre spacing x: 20 mm

Internal \varnothing ring A: 30 mm

External \varnothing ring B: 34 mm

Technical description

Internal \varnothing ring A	30 mm
Dimension D	57 mm
Version	pivotable

External Ø ring B	34 mm
Safe working load	1 t
Collar Ø support C	60 mm
Hole centre spacing x	20 mm
Internal hexagon size across flats S	6 mm
Lifting capacity WLL SF 5:1	0.8 t
Lifting capacity WLL SF 4:1	0.9 t
Thread length L	21 mm
Type of product	Eye bolt