

**Swivel eye bolt SEB, Thread Ø: M20****Order data**

Order number	086467 M20
GTIN	2050001857767
Item class	08Y

Description**Version:**

High-strength swivel eye bolts, can be rotated through 360°, painted red.

Note:

SF 5:1 = Safety Factor 5.

SF 4:1 = Safety Factor 4.

Lifting capacity WLL SF 5:1: 2 t

Lifting capacity WLL SF 4:1: 2.7 t

Thread length L: 30 mm

Hole centre spacing x: 35 mm

Internal Ø ring A: 38 mm

External Ø ring B: 45 mm

Technical description

External Ø ring B	45 mm
Safe working load	2.5 t
Internal Ø ring A	38 mm

Dimension D	80 mm
Version	pivotable
Collar Ø support C	88 mm
Hole centre spacing x	35 mm
Internal hexagon size across flats S	8 mm
Lifting capacity WLL SF 5:1	2 t
Lifting capacity WLL SF 4:1	2.7 t
Thread length L	30 mm
Type of product	Eye bolt