

**Swivel eye bolt SEB, Thread Ø: M24****Order data**

| | |
|--------------|---------------|
| Order number | 086467 M24 |
| GTIN | 2050001857897 |
| Item class | 08Y |

Description**Version:**

High-strength swivel eye bolts, can be rotated through 360°, painted red.

Note:

SF 5:1 = Safety Factor 5.

SF 4:1 = Safety Factor 4.

Lifting capacity WLL SF 5:1: 3.2 t

Lifting capacity WLL SF 4:1: 3.8 t

Thread length L: 36 mm

Hole centre spacing x: 35 mm

Internal Ø ring A: 38 mm

External Ø ring B: 45 mm

Technical description

| | |
|-------------------|-----------|
| External Ø ring B | 45 mm |
| Safe working load | 4 t |
| Version | pivotable |

| | |
|--------------------------------------|----------|
| Collar Ø support C | 88 mm |
| Dimension D | 80 mm |
| Internal Ø ring A | 38 mm |
| Hole centre spacing x | 35 mm |
| Internal hexagon size across flats S | 14 mm |
| Lifting capacity WLL SF 4:1 | 3.8 t |
| Lifting capacity WLL SF 5:1 | 3.2 t |
| Thread length L | 36 mm |
| Type of product | Eye bolt |