



Swivel eye bolt SEB, Thread Ø: M30



Order data

Order number	086467 M30
GTIN	2050001858412
Item class	08Y

Description

Version:

High-strength swivel eye bolts, can be rotated through 360°, painted red.

Note:

SF 5:1 = Safety Factor 5.

SF 4:1 = Safety Factor 4.

Lifting capacity WLL SF 5:1: 5.5 t

Lifting capacity WLL SF 4:1: 6.3 t

Thread length L: 45 mm

Hole centre spacing x: 50 mm

Internal Ø ring A: 58 mm

External Ø ring B: 70 mm

Technical description

Collar Ø support C	115 mm
Version	pivotable
Dimension D	106 mm

External Ø ring B	70 mm
Safe working load	6.3 t
Internal Ø ring A	58 mm
Hole centre spacing x	50 mm
Internal hexagon size across flats S	14 mm
Lifting capacity WLL SF 5:1	5.5 t
Lifting capacity WLL SF 4:1	6.3 t
Thread length L	45 mm
Type of product	Eye bolt