

 steinel**Heat gun, Type: 351403****Order data**

Order number	078321 351403
GTIN	4007841351403
Item class	07E

Description**Version:**

Electronically controlled **heat gun** HG 2120 E, air volume adjustment 150 – 500 l/min in 3 stages. Temperature steplessly adjustable from 80 – 630°C

Application:

For welding and forming plastics, for shrinking, removing paints, soldering, drying, and thawing.

Technical description

Air flow volume stage 3	500 l/min
Power consumption	2200 W
Air flow volume stage 1	150 l/min
Air temperature	80 - 630 °C
Air flow volume stage 2	300 l/min
Manufacturer's designation	HG 2120E
Weight	850 g
Power supply	Mains operated

Type of product

Hot air pistol

Accessories

Temperature scanner HL Scan Type 014919	078326 014919
Temperature scanner HG Scan PRO Type 007553	078325 007553
Heat gun accessory set 12 pieces Type 075569	078329 075569
Temperature scanner HG Scan PRO Type 007690	078325 007690