



## Water pump pliers with quick lever action for left-handed users, Overall length: 260 mm



### Order data

Order number	706350 260
GTIN	4000896191291
Item class	76B

### Description

#### Version:

With quick lever actuation. No need to grasp for adjustment, can be used one-handed. Jaw serration additionally induction hardened for long working life. Teeth set opposite to the direction of rotation, for a better grip. Precise spacing due to laser-cut adjustment teeth. Handles dip coated.

For left-handed users.

#### Standard:

**DIN ISO 8976**

#### Material:

Chrome vanadium steel, drop forged.

Hexagon across flats: 50 mm

Jaw capacity for pipes: 2 inch

### Technical description

Jaw capacity for pipes	2 inch
Hexagon across flats	50 mm
Handle	dip coated
Standard	DIN ISO 8976
Type of jaws	induction hardened
Material	Chrome vanadium steel, drop forged
non-sparking	no

Type of product

Pipe wrench and water pump pliers