



Reversible ratchet, 1/4 inch, 15° offset



Order data

Order number	632065
GTIN	4000896195718
Item class	630

Description

Version:

Material selection and special forging method guarantee optimal functioning and long life.

With reversing lever for right-hand and left-hand threads.

Sturdy all-steel ratchet in short slim design Particularly suitable for use in restricted spaces. With ergonomic finger supports at the end of the handle. 15° offset.

Standard:

Außenvierkante nach **DIN 3120-A 6,3** mit federnder Kugel, Innenvierkante nach **DIN 3120**.

Material:

Chrome vanadium steel, chrome-plated.

Suitable for :

Manual use.

Square drive: 1/4 in

No. of teeth: 20

Technical description

Square drive	1/4 in
overall length	89 mm
No. of teeth	20
Working angle	18 °
Material	Chrome vanadium steel
with swivel jointed head	no
with swivel head	no

with hammer function	no
with QuickRelease	no
Ratchet head can be detached from the handle	no
Twist handle	no
Type of product	Ratchet

Accessories

Replacement set, ratchet wheel	863S/7
Replacement set, ratchet wheel	863P/7N
Replacement set, shift lever	863P/6