


**Garant****Permanent magnet, transverse pole distribution, Length L: 320mm****Order data**

Order number	380040 320
GTIN	4045197781772
Item class	310

**Description****Version:**

- **Alu casing for mounting on top or for incorporation.**
- **Stop strips on 3 sides.**
- **2 switch points.**
- **Milled-in grip handle.**
- **4 ZeroClamp holes provided at 200 pitch.**
- **Lamellae made of 3 mm brass / 12 mm steel.**

2 switch points for two magnetic fields;

For large workpieces that must be clamped across the entire magnetic field, both switch points must be switched on.

**Advantage:**

Two workpieces can be clamped on a single pallet (using 2 switch points).

**Application:**

For clamping medium-sized to large workpieces for grinding, milling and spark erosion.

**Supplied with:**

Hexagon socket.

**Note:**

Suitable GARANT ZeroClamp clamping stud 360025 18M16 or 18M16/138.

The pallets are secured by ZeroClamp clamping studs or by stepless adjustable clamps securing the machine clamping slots directly to the machine table.

**Technical description**

Magnetic field height	6 mm
Nominal clamping force	130 N/cm <sup>2</sup>
Pole area length	320 mm
Weight	38 kg
Grinding allowance in pole area	6 mm
Dimension D	258 mm
Width B	320 mm
Height H	68.5 mm
Type of product	Magnetic clamping plate