

Garant**Die Left-hand thread, M-LH: M7****Order data**

Order number	140620 M7
GTIN	4062406189389
Item class	11K

Description**Version:**

Closed, pre-slit form.

1 3/4 turns lead chamfer.

Cutting direction: left-hand

Tolerance class: DIN 13 6g

Pitch: 1 mm

External Ø: 25 mm

Height: 9 mm

Technical description

External Ø	25 mm
Pitch	1 mm
Tolerance class	DIN 13 6g
Height	9 mm
Thread size	M7

Thread type	M-LH
Flank angle	60 °
Tool material	HSS
Standard	EN 22568
Cutting direction	left-hand
Type of product	Die

User data

	Suitability	V _c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions		
Steel < 500 N/mm ²	suitable		
Steel < 750 N/mm ²	suitable		
Oil	suitable		
dry	suitable only under restricted conditions		