

**Split bush, Shank \varnothing d1 / clamping \varnothing d2: 50/12mm****Order data**

| | |
|--------------|---------------|
| Order number | 319428 50/12 |
| GTIN | 4045197782120 |
| Item class | 32V |

Description**Version:**

Suitable for VDI arbors form E2 (No. 319275 – 319405).

Slotted version - alignment of the tool via fixing screws, clamping via the boring bar holder.

Application:

For \varnothing reduction for tools with plain shanks.

Technical description

| | |
|----------------------------------|------------------|
| l_1 | 90 mm |
| $\varnothing d_4$ | 55 mm |
| Clamping range $\varnothing d_2$ | 12 mm |
| Shank $\varnothing D_1$ | 50 mm |
| l_2 | 10 mm |
| Type of product | Reducing adapter |