

3M Scotch-Brite™

Bristle-Brush type C Ø 50 mm Shank Ø 6 mm, BB-ZS, Grit: 220**Order data**

Order number	573547 220
GTIN	54046719316347
Item class	53M

Description**Version:**

Cast special cleaning brushes are homogeneous grinding bodies with a mixture of precision-formed ceramic grit and Aluminium Oxide, and an **exceptionally long working life. Extremely flexible and versatile.**

The **radial** bristle brush consists of individual segments (approx. 1.6 mm wide).

Mandrel (**shank Ø 6 mm**) with cast segments.

With curved bristles (type C) for use on **profiled surfaces.**

Application:

Ensure the correct direction of rotation.

Requires no accessories for use on straight grinders or flexible shafts.

On virtually all materials, with the highest possible safety. Removal of rust, remains of adhesive, paint, light scratches and burrs. For smoothing, finishing, polishing, cleaning, and deburring.

Technical description

maximum speed	15000 min ⁻¹
Grit	220

Brush width	10 mm
Brush $\varnothing D_1$	50 mm
Colour	red
Shank $\varnothing D_s$	6 mm
Grinding medium code	Ceramic
Product name attribute	BB-ZS
Manufacturer's designation	BB-ZS
Type of product	Wheel brush