

Garant**LED torches with batteries, Type: 125mm****Order data**

Order number	081505 125
GTIN	4062406192662
Item class	01A

Description**Version:**

Long-life and very sturdy LED torch of anodised aluminium. **LED technology** with **outstanding lighting power**.

- **Tight beam with little scatter loss.**
- **High energy efficiency for long illumination time.**
- **Illuminated ring, easy to find in the dark.**
- **Splash-proof, protection class IP54.**

Homogeneous illumination via the diffusion lens, single-hand push-button switch at the front.

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Note:

For suitable batteries see No. 081551 ff.

Technical description

Battery type	Micro, AAA
Illumination time	4 - 10 h
Number of batteries contained	3
Bulb	LED module
IP Index of Protection	IP 54
Head Ø	29 mm
ATEX zone	no

Overall length	125 mm
Illumination	100 - 250 lm
Weight	119 g
Power supply	Battery-powered
Type of product	Flashlight

Accessories

Alkaline-manganese batteries International size LR3	081561 LR3
Alkaline-manganese batteries International size LR3	081552 LR3
Alkaline-manganese batteries International size LR3	081553 LR3
Alkaline-manganese batteries International size LR3	081551 LR3
Alkaline-manganese batteries International size LR3	081554 LR3
Lithium-metal batteries International size LR3	081559 LR3