

Garant**Pair of gloves Cut B, Glove size: 6****Order data**

| | |
|--------------|---------------|
| Order number | 094405 6 |
| GTIN | 4062406190576 |
| Item class | 01H |

Description**Version:**

All constituent parts including carrier material and also coating are **free of silicone** (tested by the Fraunhofer Institut). They are thus ideally suitable for use in operating areas in the automobile industry or paint shops.

Silicone-free cut-resistant gloves with very good fit and light weight. Due to the high degree of finger freedom highly suitable for precise handling of sharp-edged parts. Special yarn with Spandex **18-gauge knitted technology** and a tough polyurethane coating.

Standard:

EN 388, EN ISO 21420

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

| | |
|---------------------|----------------------|
| Glove size | 6 |
| Type of glove | Multi-purpose gloves |
| Protection category | Category II |

| | |
|-----------------------|--------------------------------|
| Contents | 12 |
| Glove characteristics | LABS free |
| Glove characteristics | Silicone-free |
| EN 388 | 4X42B |
| Backing material | Nylon / special yarn / Spandex |
| Coating | PU |
| Coating variant | The palms of the hands |
| Application range | Precision |
| Length | 180 mm |
| Colour | grey / orange |
| Knitted technology | 18G |
| Application | reusable |
| Cut protection class | B |
| Type of product | Multi-purpose gloves |