

WELDAS®**Pair of welder's safety gloves 10-2750, Glove size: 11****Order data**

Order number	094126 11
GTIN	8718564520965
Item class	06E

Description**Version:**

10-2750. Comfortable **oil and water resistant** welder's gloves of **full leather and split leather** with **COMFOflex® technology** and KEVLAR® 4-ply + 5-ply seams. With straight thumbs. **Heat resistant up to 250 °C contact heat.** Cuff with cotton lining.

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Glove size	11
Protection category	Category III
Type of glove	Welder's gloves
Glove characteristics	Flame resistance stage 4
Application	reusable
Length	360 mm
Backing material	Cowhide split leather / full leather

Material	Cowhide split leather / full leather
EN 388:2003	4143
EN 388	3133X
EN 407	423X4X
EN 12477	Type A/B
Welding processes	MIG/MAG
Colour	yellow / white
Type of product	Welder's gloves

Accessories

Welder's hand protection 44-3008LB	094135
------------------------------------	--------