

**Garant****Lever lock toolholder, right-hand, Shank / insert size: 20/09mm****Order data**

Order number	250020 20/09
GTIN	4045197781826
Item class	21T

**Technical description**

Lever screw	259018 6
Lever	259015 9
Insert size	9 mm
Shank size	20 mm
Overall length L	125 mm
Shim punches pack	259047 3
Shim	259031 27
Functional width L <sub>4</sub>	20 mm
suitable indexable insert	CN.. 09T3..
Head length L <sub>1</sub>	21 mm
Shim pins pack	259044 5
ISO code toolholder	PCBNR/L 2020K09
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	75 degrees

Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

### Accessories

Set of shim pins 10 pieces Type 5	259044 5
Shim punches set 10 pieces Type 3	259047 3
Shim Type 27	259031 27
Lever Type 9	259015 9
Lever screw Type 6	259018 6