

**Garant****Lever lock toolholder, left-hand, Shank / insert size: 16/09mm****Order data**

|              |               |
|--------------|---------------|
| Order number | 250021 16/09  |
| GTIN         | 4045197781840 |
| Item class   | 21T           |

**Technical description**

|                                 |                 |
|---------------------------------|-----------------|
| suitable indexable insert       | CN.. 09T3..     |
| Lever screw                     | 259018 6        |
| Shank size                      | 16 mm           |
| Lever                           | 259015 9        |
| Functional width L <sub>4</sub> | 16 mm           |
| Shim punches pack               | 259047 3        |
| Insert size                     | 9 mm            |
| ISO code toolholder             | PCBNR/L 1616H09 |
| Head length L <sub>1</sub>      | 20 mm           |
| Shim                            | 259031 27       |
| Overall length L                | 100 mm          |
| Shim pins pack                  | 259044 5        |
| Standard                        | Works standard  |
| Application type                | left-hand       |
| Through-coolant                 | no              |
| Setting angle κ                 | 75 degrees      |

|                 |                               |
|-----------------|-------------------------------|
| Application     | External longitudinal turning |
| Application     | External longitudinal turning |
| Application     | External longitudinal turning |
| Type of product | Boring bar                    |

### Accessories

|                                  |           |
|----------------------------------|-----------|
| Set of shim pins10 pieces Type 5 | 259044 5  |
| Shim Type 27                     | 259031 27 |
| Lever screw Type 6               | 259018 6  |
| Lever Type 9                     | 259015 9  |
| Shim punches set10 pieces Type 3 | 259047 3  |