

Garant**Lever lock toolholder, right-hand, Shank / insert size: 20/09mm****Order data**

Order number	250022 20/09
GTIN	4045197781888
Item class	21T

Technical description

Insert size	9 mm
Overall length L	125 mm
Lever screw	259018 6
suitable indexable insert	CN.. 09T3..
Shim punches pack	259047 3
Shank size	20 mm
Shim	259031 27
Shim pins pack	259044 5
Head length L ₁	20 mm
Functional width L ₄	25 mm
Lever	259015 9
ISO code toolholder	PCKNR/L 2020K09
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	75 degrees

Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Set of shim pins10 pieces Type 5	259044 5
Lever Type 9	259015 9
Shim Type 27	259031 27
Lever screw Type 6	259018 6
Shim punches set10 pieces Type 3	259047 3