

**Garant****Lever lock toolholder, left-hand, Shank / insert size: 16/09mm****Order data**

Order number	250023 16/09
GTIN	4045197782601
Item class	21T

**Technical description**

Head length L <sub>1</sub>	22 mm
Functional width L <sub>4</sub>	20 mm
Shim pins pack	259044 5
ISO code toolholder	PCKNR/L 1616H09
Shank size	16 mm
Shim	259031 27
Overall length L	100 mm
Insert size	9 mm
Shim punches pack	259047 3
Lever screw	259018 6
suitable indexable insert	CN.. 09T3..
Lever	259015 9
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle κ	75 degrees

Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

### Accessories

Shim Type 27	259031 27
Lever Type 9	259015 9
Lever screw Type 6	259018 6
Set of shim pins 10 pieces Type 5	259044 5
Shim punches set 10 pieces Type 3	259047 3