

**Garant**
**Lever lock toolholder, left-hand, Shank / insert size: 32/16mm**

**Order data**

Order number	250023 32/16
GTIN	4045197782649
Item class	21T

**Technical description**

Lever	259015 12
Shim punches pack	259047 4
Head length L <sub>1</sub>	34 mm
Shank size	32 mm
Overall length L	170 mm
Shim pins pack	259044 6
Lever screw	259018 11
Insert size	16 mm
Functional width L <sub>4</sub>	40 mm
Shim	259031 35
ISO code toolholder	PCKNR/L 3232P16
suitable indexable insert	CN.. 1606..
Series	QuickTurn
Standard	Works standard
Application type	left-hand
Through-coolant	no

Setting angle $\kappa$	75 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Shim punches set 10 pieces Type 4	259047 4
Shim Type 35	259031 35
Set of shim pins 10 pieces Type 6	259044 6
Lever Type 12	259015 12
Lever screw Type 11	259018 11