

Garant
Lever lock toolholder, right-hand, Shank / insert size: 25/16mm

Order data

Order number	250022 25/16
GTIN	4045197782663
Item class	21T

Technical description

Shim	259031 35
Overall length L	150 mm
Head length L ₁	30 mm
Lever	259015 12
ISO code toolholder	PCKNR/L 2525M16
suitable indexable insert	CN.. 1606..
Shank size	25 mm
Lever screw	259018 11
Shim pins pack	259044 6
Shim punches pack	259047 4
Insert size	16 mm
Functional width L ₄	32 mm
Series	QuickTurn
Standard	Works standard
Application type	right-hand
Through-coolant	no

Setting angle κ	75 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Lever Type 12	259015 12
Set of shim pins 10 pieces Type 6	259044 6
Shim punches set 10 pieces Type 4	259047 4
Lever screw Type 11	259018 11
Shim Type 35	259031 35