

**Grip wrench with pivoted lower jaw, overall length: 250mm****Order data**

Order number	708903 250
GTIN	3662424019845
Item class	73R

Description**Version:**

Easy and safe to use. Trouble-free and quick opening by the **release lever** on the lower handle. With large clamping range and clamping depth, 5-step quick adjustment and additional fine adjustment. Lower jaw deeply cranked for clamping U-shaped and angle profiles, pipes etc. Serrated gripping jaws and special stable spring steel body. Fully nickel-plated.

Application:

For secure gripping of profiled, flat, and tubular materials. Clamping force adjustable up to 10,000 N.

Material:

Chrome molybdenum vanadium steel jaws; drop forged.

Technical description

Jaw capacity angled materials	50 mm
Jaw length	60 mm
overall length	250 mm
Jaw capacity round materials	110 mm
Type of product	Grip wrench